

Electrical sub-base VAVE-L1-1VL2-LP

Part number: 566723

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	24 V
Immunity to surge	0.8 kV
Pollution degree	3
Extended ambient temperature	-5 - 60 °C
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C ... 50 °C
Mounting position	Any
Product weight	7.8 g
Connection cross section	0.14 mm ²
Electrical connection	Stranded conductor
Cable length	1 m
Wire ends	Wire ferrule
Protective conductor connection	Not provided
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS compliant
Material housing	Process automation