

Electrical sub-base VAVE-L1-1L3-LR

Part number: 566728

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Reverse polarity protection	For operating voltage
Additional functions	Spark arresting Holding current reduction
Signal status display	LED
Nominal operating voltage DC	24 V
Immunity to surge	0.8 kV
Pollution degree	3
Approval	RCM
CE mark (see declaration of conformity)	To EU EMC Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Product weight	17.5 g
Connection cross section	0.14 mm ²
Electrical connection	Stranded conductor
Cable length	2.5 m
Wire ends	Wire ferrule
Protective conductor connection	Not provided
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS compliant
Material housing	Process automation