

Plastic tubing PUN-14X2-SW

Part number: 570391

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	14 mm
Flow-relevant bending radius	84 mm
Inside diameter	9.8 mm
Min. bending radius	45 mm
Instructions on use	TPE-U, ester-based The plastic tubing can only be installed in contact with cables if the sheathing is free from phosphoric acid esters. Otherwise the plastic tubing can get damaged.
Tubing characteristics	Suitable for energy chains
Operating pressure complete temperature range	-0.095 MPa ... 0.7 MPa
Operating pressure complete temperature range	-0.95 bar ... 7 bar
Operating pressure complete temperature range	-13.775 psi ... 101.5 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1 MPa
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-13.775 psi ... 145 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Fire test material	UL94 HB
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C ... 60 °C
Product weight according to length	0.0949 kg/m
Pneumatic connection	For push-in connector outer diameter of 14 mm
Colour	Black
Shore hardness	D 52 +/-3
Note on materials	RoHS compliant
Material tubing	TPE-U(PU)