


Electrical sub-base VAVE-L1-1VK8-LP

Part number: 573943

FESTO



Data sheet

 General operating condition

Feature	Value
Cable characteristic	For static applications
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V
Immunity to surge	0.8 kV
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	47 g
Electrical connection	Square design/open end
Cable structure	2 x 0.25 mm ²
Cable diameter	3.4 mm
Cable diameter tolerance	± 0.1 mm
Cable length	2.5 m
Wire ends	Wire ferrule
Protective conductor connection	Not provided
Type of mounting	On solenoid valve via self-tapping screw
Housing colour	Black
Note on materials	RoHS compliant
Material cover	Process automation
Material seals	EPDM
Material housing	Process automation
Material cable sheath	TPV
Material screws	Tempered steel