



Vertical pressure supply plate VABF-L1-P3A3-G18

Part number: 574593

FESTO



Data sheet

 General operating condition

Feature	Value
Grid dimension	16 mm
Max. number of valve positions	1
Symbol	00995306
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Approval	RCM c UL us - Recognised (Oil)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque for valve mounting	0.65 Nm
Product weight	350 g
Pneumatic connection, port 1	G1/8
Note on materials	RoHS compliant
Material plate	Wrought aluminium alloy