

# Manifold block VABM-B10-20S-G14-10

Part number: 576425

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Grid dimension	22 mm
Mounting position	Any
Max. number of valve positions	10
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1108 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 5	G1/4
Note on materials	RoHS compliant
Material manifold rail	Wrought aluminium alloy