

Push-in sleeve NPQH-D-S14-E-P10

Part number: 578322

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal size	12 mm
Mounting position	Any
Design	Straight design
Size of pack	10
Symbol	00997424
Operating pressure complete temperature range	-0.095 MPa ... 2 MPa
Operating pressure complete temperature range	-0.95 bar ... 20 bar
Operating pressure complete temperature range	-13.775 psi ... 290 psi
Note on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Certificate issuing authority	NSF C0523185
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See declaration of conformity NSF/ANSI 169
Ambient temperature	0 °C ... 150 °C
Product weight	19.1 g
Pneumatic connection, port 1	Push-in sleeve Ø 14 mm
Pneumatic connection, port 2	Push-in sleeve Ø 14 mm
Note on materials	RoHS compliant
Material housing	Brass, chemically nickel-plated