

# Electrical adapter SASC-P4-A-M8-A

Part number: 8000326

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value  |
|--|--|
| Corrosion resistance class CRC                       | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                               | VDMA24364-B1/B2-L  |
| Degree of protection                                 | IP40   |
| Electrical connection 1, connection type             | Plug   |
| Electrical connection 1, cable outlet                | Straight, angled   |
| Electrical connection 1, connector system            | M8x1, A-coded, to EN 61076-2-104<br>Diameter 8 mm, A-coded to EN 61076-2-104 |
| Electrical connection 1, number of connections/cores | 4  |
| Electrical connection 1, used connections/cores      | 4  |
| Electrical connection 1, type of mounting            | Snap-locking<br>Screw-type lock<br>Not rotatable                             |
| Electrical connection 1, compatible type of mounting | Compatible with latching lock<br>Compatible with rotatable screw-type lock   |
| Type of mounting                                     | Threaded   |
| Housing colour                                       | Black  |
| Note on materials                                    | RoHS compliant   |
| Material housing                                     | Reinforced PA  |
| Material screws                                      | High-alloy steel   |