

Electrical adapter SASC-P4-A-M8-S

Part number: 8000327

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP40 |
| Electrical connection 1, connection type | Plug |
| Electrical connection 1, cable outlet | Straight, angled |
| Electrical connection 1, connector system | M8x1, A-coded, to EN 61076-2-104 Diameter 8 mm, A-coded to EN 61076-2-104 |
| Electrical connection 1, number of connections/cores | 4 |
| Electrical connection 1, used connections/cores | 4 |
| Electrical connection 1, type of mounting | Snap-locking Screw-type lock Not rotatable |
| Electrical connection 1, compatible type of mounting | Compatible with latching lock Compatible with rotatable screw-type lock |
| Type of mounting | Threaded |
| Housing colour | Black |
| Note on materials | RoHS compliant |
| Material housing | Reinforced PA |
| Material screws | High-alloy steel |