

Flow control VFFG-T-M5-5

Part number: 8025709

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Valve function | Flow control function |
| Type of mounting | With thread |
| Standard nominal flow rate in flow control direction | 9.6 l/min |
| Operating pressure | -0.9 bar ... 10 bar |
| Ambient temperature | -5 °C ... 60 °C |
| Nominal size | 0.5 mm |
| b value | 0.5 |
| C value | 0.04 l/sbar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 60 °C |
| Product weight | 0.5 g |
| Note on materials | RoHS compliant |
| Material hollow bolt | Process automation |