

Common supply manifold VABM-B10-25-G12-8-P53

Part number: 8026225

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	27.5 mm
Mounting position	Any
Max. number of valve positions	8
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	750 g
Type of mounting	With mounting bracket
Pneumatic connection, port 1	G1/2
Note on materials	RoHS compliant
Material manifold rail	Wrought aluminium alloy