

Manifold block VABM-B10-25S-G38-5-P3

Part number: 8026300

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	27.5 mm
Mounting position	Any
Max. number of valve positions	5
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	726 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G3/8
Note on materials	RoHS compliant
Material manifold rail	Wrought aluminium alloy