

Manifold block VABM-B10-30E-G34-8

Part number: 8026365

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|-------------------------------|
| Grid dimension | 32 mm |
| Mounting position | Any |
| Max. number of valve positions | 8 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 4665 g |
| Type of mounting | With through-hole |
| Pilot air port 12 | G1/8 |
| Pilot air port 14 | G1/8 |
| Pneumatic connection, port 1 | G3/4 |
| Pneumatic connection, port 3 | G3/4 |
| Pneumatic connection, port 5 | G3/4 |
| Note on materials | RoHS compliant |
| Material manifold rail | Wrought aluminium alloy |