

T-fitting NPFC-T-2R14-G14-MMF

Part number: 8030260

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|--|
| Material threaded fitting | Brass, nickel-plated |
| Size of pack | 10 |
| Operating pressure | -0.95 bar ... 50 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [-::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 150 °C |
| Product weight | 40.3 g |
| Pneumatic connection, port 1 | R1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Note on materials | RoHS compliant |