

# Extension NPFC-E1-2G38-FM

Part number: 8030300

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                                    |
|--------------------------------|--|
| Material threaded fitting      | Brass, nickel-plated                     |
| Size of pack                   | 10                                       |
| Operating pressure             | -0.95 bar ... 50 bar                     |
| Operating medium               | Compressed air to ISO 8573-1:2010 [-::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress                 |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                        |
| Ambient temperature            | -20 °C ... 150 °C                        |
| Product weight                 | 47.56 g                                  |
| Pneumatic connection, port 1   | G3/8                                     |
| Pneumatic connection, port 2   | G3/8                                     |
| Note on materials              | RoHS compliant                           |