

# Reducing nipple NPFC-R-G14-G18-MF

Part number: 8030308

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                                     |
|--------------------------------|---|
| Material threaded fitting      | Nickel-plated brass                       |
| Size of pack                   | 10  |
| Operating pressure             | -0.95 bar ... 50 bar                      |
| Operating medium               | Compressed air to ISO 8573-1:2010 [-:~:-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress                  |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                         |
| Ambient temperature            | -20 °C ... 150 °C                         |
| Product weight                 | 10.8 g                                    |
| Pneumatic connection, port 1   | G1/4                                      |
| Pneumatic connection, port 2   | G1/8                                      |
| Note on materials              | RoHS-compliant                            |