

Sealing rings OL-...-RR

Ø M5, M10, M12, M14, M16, M22, G1/8, G1/4, G3/8, G1/2, G3/4

Cleanroom class ISO 4 (FS209E class 10)

This captive sealing ring is effective even when only gently tightened, is reusable and can be used at hydraulic pressures of up to 30 bar.

OL-...-RR

Operating pressure: -1 ... +30 bar
Temperature range: -30 ... +100 °C



Type	Part No.	For thread	Material	Max. permissible tightening torque	Weight [kg]
OL-M5-RR	15024659	M5	Stainless steel & NBR	2 Nm	0.001
OL-1/8-RR	15024660	G1/8		4 Nm	
OL-1/4-RR	15024661	G1/4		11 Nm	
OL-3/8-RR	15024662	G3/8	Al & NBR	40 Nm	0.002
OL-1/2-RR	15024663	G1/2		50 Nm	
OL-3/4-RR	15024664	G3/4		100 Nm	
OL-M6-RR	15024665	M6	St. steel & NBR	-	0.001
OL-M10-RR	15024666	M10	Al & NBR	12 Nm	0.006
OL-M12-RR	15024667	M12		20 Nm	0.007
OL-M14-RR	15024668	M14		35 Nm	0.008
OL-M16-RR	15024669	M16		-	0.096
OL-M22-RR	15024670	M22		-	0.025