

# Terminating resistor CACR-S-B12G5-220-PB

Part number: 1072128

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Operational voltage range DC	0 V ... 5 V
Pollution degree	3
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP67
Ambient temperature	-25 °C ... 80 °C
Product weight	11.6 g
Electrical connection	M12x1 Straight plug
Plug encoding	B
Note on materials	RoHS-compliant
Material housing	TPE-U(PU)
Material electrical contact	Brass Bronze