

# Pressure gauge PAGL-HP3-63-60-G14

Part number: 1166938

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Indicating range	0 bar ... 60 bar
Indicating range	0 MPa ... 6 MPa
Indicating range	0 psi ... 870 psi
Symbol	00991463
Conforms to standard	EN 837-1
Nominal size of pressure gauge	63
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Design	Bourdon tube pressure gauge
Type of mounting	Inline installation
Operating medium	Inert gas Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa ... 6 MPa
Operating pressure	0 bar ... 60 bar
Operating pressure	0 psi ... 870 psi
Alternating load factor	0.66
Measurement accuracy class	1.6
Degree of protection	IP65
Storage temperature	-40 °C ... 70 °C
Media temperature	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Note on materials	RoHS compliant
Position of connection	Centred, rear
Pneumatic connection	G1/4
Material in contact with the medium	Brass
Material screwed plug	Brass
Material housing	Steel
Material screen	Horse power

<b>Feature</b>	<b>Value</b>
Housing colour	Silver
Product weight	80 g
Scale	Triple scale MPa (outer scale) Bar (external) psi (inner scale)