

# Coupling EAMC-40-66-12-15

Part number: 123850

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting diameter 1	12 mm
Mounting diameter 2	15 mm
Size	40
Nominal length	66 mm
Mounting position	Any
Max. rotational speed	6500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	42.3 kgmm <sup>2</sup>
Transmittable torque	21 Nm
Product weight	139 g
Note on materials	RoHS compliant