

# Bellow gripper DHEB-27-E-D-E-P

Part number: 1320793

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	27
Stroke of bellows	12 mm
Min. $\varnothing$ to be gripped	28 mm
Max. $\varnothing$ to be gripped	37 mm
Mounting position	optional
Mode of operation	Single-acting Closed
Gripper function	Adaptive
Design	Contracting diaphragm Force pilot operated motion sequence
Guide	Basic guide
Position detection	Via proximity switch
Operating pressure	4 bar ... 8 bar
Reset pressure	<1 bar
Max. operating frequency of gripper	$\leq 4$ Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	30 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	60 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	5 °C ... 60 °C
Average replacement interval for the bellows	0.5 MioCyc
Guide value for effective load	0.45 kg
Product weight	79 g
Type of mounting	Via male thread Via lock nut
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material bellows	EPDM
Material housing	Aluminium Anodised