

Pressure gauge MA-15-145-M5-PSI

Part number: 132341

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Indicating range	0 psi ... 145 psi
Symbol	00991463
Nominal size of pressure gauge	15
Design	Bourdon tube pressure gauge without measuring mechanism
Type of mounting	Inline installation
Operating medium	Inert gas Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating pressure	0 psi ... 145 psi
Alternating load factor	0.66
Measurement accuracy class	5
Degree of protection	IP53
Media temperature	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS compliant
Position of connection	Centred, rear
Pneumatic connection	M5
Material screwed plug	Brass
Material housing	Steel
Material screen	Makrolon®
Housing colour	Black
Product weight	10 g
Scale	Single scale psi (outer scale)