

Flow control/silencer VFFK-C-K-R18-P

Part number: 133142

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Valve function | Sound pressure control function |
| Selection of additional functions | With silencer |
| Pneumatic connection, port 1 | R1/8 |
| Adjustment component | Knurled screw |
| Type of mounting | Screw-in |
| Standard flow rate 0.6- \rightarrow 0 MPa (6- \rightarrow 0 bar, 87- \rightarrow 0 psi) | 0 l/min ... 270 l/min |
| Operating pressure | 0 bar ... 10 bar |
| Ambient temperature | 0 °C ... 60 °C |
| Type of seal on screwed plug | Coating |
| Mounting position | optional |
| Symbol | 00991451 |
| Operating pressure complete temperature range | 0 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | 0 °C ... 60 °C |
| Product weight | 13.5 g |
| Material shock absorber insert | PE |
| Material screwed plug | Nickel-plated brass |
| Note on materials | RoHS-compliant |
| Material adjusting screw | Nickel-plated brass |