

Barbed fitting CRCN-1/8-PK-4

Part number: 13970

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	3.2 mm
Type of seal on screwed plug	Sealing ring
Size of pack	10
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	0 °C ... 60 °C
Product weight	7.86 g
Pneumatic connection, port 1	Male thread G1/8
Pneumatic connection, port 2	For tubing outside diameter of 6 mm
Note on materials	RoHS-compliant
Material housing	High-alloy stainless steel
Material thread seal	PA-reinforced TPE-U(PU)