

Coupling EAMD-25-22-10-10X12

Part number: 1453860

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Mounting diameter 1 | 10 mm |
| Mounting diameter 2 | 10 mm |
| Size | 25 |
| Nominal length | 22 mm |
| Mounting position | Any |
| Max. rotational speed | 8000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 3.2 kgmm ² |
| Transmittable torque | 9 Nm |
| Product weight | 43.7 g |
| Note on materials | RoHS compliant |