

Quick coupling socket KD1-M3-A

Part number: 151995

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	1.5 mm
Operating pressure complete temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Operating pressure complete temperature range	-13.775 psi ... 174 psi
Standard nominal flow rate (standardised to DIN 1343)	44 l/min
Nominal flow rate standardised according to ISO 8778	47.7 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal torque	0.6 Nm
Tolerance for nominal tightening torque	±10%
Product weight	2.9 g
Pneumatic connection, port 1	Male thread M3
Note on materials	RoHS compliant
Material seals	NBR
Material spring	High-alloy stainless steel
Material housing	Brass, nickel-plated
Material thread seal	NBR High-alloy stainless steel
Material thread piece	Brass, nickel-plated
Material ball	High-alloy stainless steel
Valve body material	Brass
Material releasing sleeve	Brass, nickel-plated