

Semi-rotary drive DRRD-35-180-FH-PA

Part number: 1526825

FESTO



 General operating condition

Data sheet

Feature	Value
Size	35
Cushioning angle	36 deg
Setting range of swivel angle for each end position	+10 /-150 deg
Swivel angle	180 deg
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Design	Rack and pinion
Position detection	Via proximity switch
Symbol	00991265
Operating pressure	0.3 MPa ... 0.8 MPa
Operating pressure	3 bar ... 8 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	15.8 Nm
Permissible mass moment of inertia	0.25 kgm ²
Product weight	4510 g
Type of mounting	With through-hole With female thread
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material drive shaft	Tempered steel
Material cover	Aluminium anodised
Material seals	NBR TPE-U(PU)
Material housing	Smooth-anodised