


Check valve HB-3/8-QS-10

Part number: 153457

FESTO



Data sheet

 [General operating condition](#)

| Feature | Value |
|---|--|
| Valve function | Non-return function |
| Pneumatic connection, port 1 | QS-10 |
| Pneumatic connection, port 2 | R3/8 |
| Type of mounting | Screw-in |
| Standard nominal flow rate (standardised to DIN 1343) | 1700 l/min |
| Operating pressure | -1 bar ... 10 bar |
| Ambient temperature | 0 °C ... 60 °C |
| Material housing | Anodised aluminium |
| Housing colour | Silver |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Symbol | 00991455 |
| Min. diff. pressure, opening | 0.1 bar |
| Min. diff. pressure, closing | 0.2 bar |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 47 g |
| Note on materials | RoHS-compliant |