


Air reservoir CRVZS-0.1

Part number: 160233

FESTO



 General operating condition

Data sheet

Feature	Value
Volume	0.1 l
Mounting position	Any
Conforms to standard	AD 2000
Symbol	00991528
Operating pressure	-0.095 MPa ... 1.6 MPa
Operating pressure	-0.95 bar ... 16 bar
Operating pressure	-13.78 psi ... 232 psi
Approval	German Technical Control Board (TÜV)
Operating medium	Compressed air to ISO 8573-1:2010 [-:--:] Nitrogen
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitable for use with food	See supplementary material information
Media temperature	-10 °C ... 100 °C
Ambient temperature	-10 °C ... 100 °C
Max. tightening torque for connecting thread	15 Nm
Product weight	226 g
Type of mounting	Via retaining clips
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material air reservoir	High-alloy stainless steel
Material fixing clips	High-alloy stainless steel