


Air reservoir CRVZS-0.4

Part number: 160234

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|---|
| Volume | 0.4 l |
| Mounting position | Any |
| Conforms to standard | AD 2000 |
| Symbol | 00991528 |
| Operating pressure | -0.095 MPa ... 1.6 MPa |
| Operating pressure | -0.95 bar ... 16 bar |
| Operating pressure | -13.78 psi ... 232 psi |
| Approval | German Technical Control Board (TÜV) |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:--:] Nitrogen |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitable for use with food | See supplementary material information |
| Media temperature | -10 °C ... 100 °C |
| Ambient temperature | -10 °C ... 100 °C |
| Max. tightening torque for connecting thread | 23 Nm |
| Product weight | 543 g |
| Type of mounting | Via retaining clips |
| Pneumatic connection | G1/4 |
| Note on materials | RoHS compliant |
| Material air reservoir | High-alloy stainless steel |
| Material fixing clips | High-alloy stainless steel |