

Vacuum filter VAF-PK-6

Part number: 160239

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal size | 4.6 mm |
| Mounting position | optional |
| Grade of filtration | 50 µm |
| Symbol | 00991483 |
| Operating pressure | -0.95 bar ... 0 bar |
| Note on operating pressure | Only for use in open vacuum systems |
| Flow rate with vacuum = -0.075 MPa (-0.75 bar, -10.875 psi) | 210 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Ambient temperature | 0 °C ... 40 °C |
| Product weight | 10 g |
| Type of mounting | In-line installation |
| Pneumatic connection | PK-6 with union nut |
| Material union nut | POM |
| Note on materials | RoHS-compliant |
| Material filter | Fabric PA |
| Material housing | PA |
| Suitable for ejector pulse | ≤8 bar |