

Angled plug socket PEV-1/4-A-WD

Part number: 161209

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	With through-hole
Electrical connection	4-pin Angled socket
Degree of protection	IP65
Ambient temperature	-40 °C ... 90 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant