

Filter combination LFMBA-1/2-D-MIDI-A

Part number: 162670

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Midi
Series	D
Mounting position	Vertical +/-5°
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	Fully automatic
Design	Fibre filter
Max. condensate volume	43 ml
Bowl guard	Metal bowl guard
Symbol	00991551
Operating pressure	1.5 bar ... 12 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:7:2] Inert gases
Media temperature	1.5 °C ... 60 °C
Residual oil content	0.01 mg/m ³
Ambient temperature	-10 °C ... 60 °C
Product weight	1300 g
Type of mounting	With accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Note on materials	RoHS-compliant
Material filter	Borosilicate fibre
Material housing	Die-cast zinc
Material bowl	PC