

# Blanking plug CQC-22H

Part number: 177715

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                       | Value  |
|---|--|
| Mounting position                             | Any  |
| Size of pack                                  | 1  |
| Design  | Push-pull principle  |
| Operating pressure complete temperature range | -0.95 bar ... 7 bar  |
| Temperature-dependent operating pressure      | -0.95 bar ... 15 bar   |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:-:-]  |
| Note on operating and pilot medium            | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                        | VDMA24364 zone III   |
| Suitable for use with food                    | See supplementary material information   |
| Ambient temperature                           | -25 °C ... 70 °C   |
| Product weight                                | 10 g   |
| Pneumatic connection, port 1                  | Push-in sleeve CQ-22   |
| Pneumatic connection, port 2                  | Push-in sleeve CQ-22   |
| Note on materials                             | RoHS compliant   |
| Material blanking plug                        | POM  |