

Fluid separator CQA-22

Part number: 177716

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	12 mm
Mounting position	optional
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.95 bar ... 7 bar
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Media temperature	-25 °C ... 75 °C
Ambient temperature	-25 °C ... 70 °C
Product weight	76 g
Pneumatic connection, port 1	For pipe/tubing O.D. 22 mm
Pneumatic connection, port 2	For pipe/tubing outside diameter of 22 mm
Note on materials	RoHS-compliant
Material housing	POM
Material release ring	POM
Material tubing clamp component	High-alloy stainless steel