

Suction cup with connection ESS-10-SNA

Part number: 189288

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Min. workpiece radius	30 mm
Nominal size	2 mm
Suction cup diameter	10 mm
Suction cup volume	0.05 cm ³
Position of connection	Top
Mounting position	optional
Special characteristics	Antistatic
Symbol	00991485
Correlation to suction-cup holder	Size 3
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.07 MPa
Nominal operating pressure	-0.7 bar
Nominal operating pressure	-10.15 psi
Surface resistance	≤2.0E-4 MOhm
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C ... 70 °C
Holding force at nominal operating pressure	3.9 N
Lateral force at nominal operating pressure	7.5 N
Product weight	1.5 g
Type of mounting	Via vacuum port
Vacuum connection	M4
Colour	Black/white dot
Shore hardness	50 +/- 5
Material screwed plug	Nickel-plated brass
Note on materials	RoHS-compliant

Feature	Value
Material suction cup	NBR