

Suction cup with connection ESS-15-SS

Part number: 189291

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Min. workpiece radius | 35 mm |
| Nominal size | 2 mm |
| Suction cup diameter | 15 mm |
| Suction cup volume | 0.208 cm ³ |
| Position of connection | Top |
| Mounting position | optional |
| Symbol | 00991485 |
| Correlation to suction-cup holder | Size 3 |
| Suction cup shape | Round, flat |
| Operating pressure | -0.095 MPa ... 0 MPa |
| Operating pressure | -0.95 bar ... 0 bar |
| Operating pressure | -13.775 psi ... 0 psi |
| Nominal operating pressure | -0.07 MPa |
| Nominal operating pressure | -0.7 bar |
| Nominal operating pressure | -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | -30 °C ... 180 °C |
| Holding force at nominal operating pressure | 8.5 N |
| Lateral force at nominal operating pressure | 6.5 N |
| Product weight | 1.9 g |
| Type of mounting | Via vacuum port |
| Vacuum connection | M4 |
| Colour | Transparent |
| Shore hardness | 50 +/- 5 |
| Material screwed plug | Nickel-plated brass |
| Note on materials | RoHS-compliant |
| Material suction cup | VMQ (silicone) |