

Blanking plug CQC-28H

Part number: 194590

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.95 bar ... 7 bar
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	-25 °C ... 70 °C
Product weight	22 g
Pneumatic connection, port 1	Push-in sleeve CQ-28
Pneumatic connection, port 2	Push-in sleeve CQ-28
Note on materials	RoHS compliant
Material blanking plug	POM