

Barbed T-fitting TCN-M5-PK-2

Part number: 19525

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	1.3 mm
Type of seal on screwed plug	Sealing ring
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Pneumatic connection, port 1	Male thread M5
Pneumatic connection, port 2	For tubing outer diameter of 3 mm
Note on materials	RoHS-compliant
Material housing	Steel Die-cast zinc