

Electrical plug-in base MHAP-PI

Part number: 197260

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	Clip
Mounting position	optional
Product weight	4 g
Electrical connection	2-pin Socket
Operational voltage range DC	≤60 V
Permissible current load	3 A
Cable length	0.5 m
Cable diameter	1 mm
Cable structure	2 x 0.14 mm ²
Degree of protection	IP40
Ambient temperature	-20 °C ... 80 °C
Ambient temperature with moving cable	-20 °C ... 50 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA
Material electrical contact	Copper alloy, tin-plated