

Silencer UO-1/4

Part number: 197584

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Design	Open silencer
Symbol	00991473
Operating pressure	0 MPa ... 0.8 MPa
Operating pressure	0 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	8 g
Pneumatic connection	G1/4
Material shock absorber insert	Packaging unit
Material screwed plug	Packaging unit
Note on materials	RoHS compliant