

Spiral plastic tubing PUN-6X1-S-2-BL

Part number: 197591

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Working length | 2 m |
| Outside diameter | 6 mm |
| Block length | 0.518 m |
| Inside diameter | 4 mm |
| Winding diameter | 46 mm |
| Number of turns | 52 |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi |
| Approval | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0527 00 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -35 °C ... 60 °C |
| Product weight | 110 g |
| Pneumatic connection | For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut For barbed fitting I.D. 4 mm |
| Colour | Blue |
| Shore hardness | D 52 +/-3 |
| Material tubing | TPE-U(PU) |