

# DUO spiral plastic tubing PUN-12X2-S-1-DUO-BS

Part number: 197629

FESTO



 General operating condition

## Data sheet

| Feature                                  | Value   |
|--|---|
| Working length                           | 1 m   |
| Outside diameter                         | 12 mm   |
| Block length                             | 0.44 m  |
| Inside diameter                          | 8 mm  |
| Winding diameter                         | 95 mm   |
| Number of turns                          | 9   |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa                            |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar                            |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi                         |
| Approval                                 | German Technical Control Board (TÜV)            |
| Certificate issuing authority            | B 013277 0527 00                                |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-]       |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                  |
| Ambient temperature                      | -35 °C ... 60 °C                                |
| Product weight                           | 390 g   |
| Pneumatic connection                     | For push-in connector outside diameter of 12 mm |
| Colour                                   | Blue/black                                      |
| Shore hardness                           | D 52 +/-3                                       |
| Material tubing                          | TPE-U(PU)                                       |