

# Barbed hose fitting N-3/4-P-19

Part number: 3613

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal size	16.5 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	Straight design
Size of pack	1
Operating pressure complete temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	40 Nm
Product weight	32.74 g
Pneumatic connection, port 1	Male thread G3/4
Pneumatic connection, port 2	For tubing I.D. 19 mm
Note on materials	RoHS-compliant
Material housing	Anodised aluminium