

# Silencer U-PK-4

Part number: 4932

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	optional
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate to atmosphere	580 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	77 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	4.1 g
Pneumatic connection	PK-4
Material shock absorber insert	Bronze
Material screwed plug	Brass
Note on materials	RoHS-compliant