

Coupling EAMD-42-40-22-16X25

Part number: 5046328

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|----------------------|
| Mounting diameter 1 | 22 mm |
| Mounting diameter 2 | 16 mm |
| Size | 42 |
| Nominal length | 40 mm |
| Mounting position | Any |
| Max. rotational speed | 6000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 39 kgmm ² |
| Transmittable torque | 17 Nm |
| Product weight | 186 g |
| Note on materials | RoHS compliant |