

# Control element VAOH-P15-H13

Part number: 5196471

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Stroke                         | 20 mm                         |
| Piston diameter                | 50 mm                         |
| Mounting position              | optional                      |
| Position detection             | Via proximity switch          |
| Operating pressure             | ≤1 bar                        |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity         | VDMA24364 zone III            |
| Product weight                 | 1350 g                        |
| Pneumatic connection, port 1   | G1/8                          |
| Note on materials              | RoHS-compliant                |