

Micro-filter cartridge MS6-LFM-A

Part number: 532909

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | 6 |
| Based on standard | ISO 12500-1 ISO 12500-3 |
| Series | MS |
| Grade of filtration | 0.01 µm |
| Max. standard flow rate for clean air class | 900 l/min |
| Min. standard flow rate for clean air class | 135 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [6:-:4] Inert gases |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [3:-:2] |
| Fractional filtration efficiency (0,1 - 0,5 µm) | 99.995 % |
| MPPS | 0.05 µm |
| Filter efficiency MPPS | 99.95 % |
| Residual oil content | 0.01 mg/m ³ |