


Silencer UC-M5-50

Part number: 534217

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Size of pack	50
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate to atmosphere	350 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	60 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	0.4 g
Pneumatic connection	M5
Material shock absorber insert	Packaging unit
Material screwed plug	Packaging unit
Note on materials	RoHS compliant