

# Ball valve VAPB-2 1/2-F-25-F07

Part number: 534310

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Design	2-way ball valve
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Inline installation
Connection Process valve	Rp2 1/2
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F07
Inside diameter	63 mm
Nominal size DN	65
Valve function	2/2
Flow direction	Reversible
Nominal pressure PN	25
Breakaway torque at differential pressure, nominal pressure, process valve PN	45 Nm
Break-away torque at a differential pressure of 1 MPa (10 bar, 145 psi)	33 Nm
Based on standard	ISO 5211
Symbol	00991458
Medium	Compressed air to ISO 8573-1:2010 [-:-:-] Inert gases Water Neutral fluids
Media temperature	-20 °C ... 150 °C
Flow rate Kv	535 m <sup>3</sup> /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Brass, nickel-plated
Material number housing	2,0402 CW617N
Material seat seal	PTFE

<b>Feature</b>	<b>Value</b>
Material seals	HNBR PTFE
Material ball	Brass Hard chrome-plated
Material number ball	2,0402 CW617N
Material shaft	Brass
Material number shaft	2,0401 CW614N
Product weight	3100 g
Corrosion resistance class CRC	1 - Low corrosion stress